

Static Pass Box

Fitted only between two cleanroom areas of the same classification levels and has no Ventilation (air supply or extract) provision.

It is also known as a passive pass box and is equipped with UV Light It's mainly used for non-complex, quick transfers of products in the same classification of Air.





Dynamic Pass Box

Fitted between clean room areas of different classification levels and Material is passed through vertically HEPA filtered air.
Also called Active Pass Box and they are

equipped with UV light.







Static Pass Box



Outside Dimension (W×D×H) (mm)	Inside Dimension (W×D×H) (mm)
600×460×530	400×400×400
700×560×630	500×500×500
800×660×730	600×600×600
900×760×830	700×700×700
1000×860×930	800×800×800

All kinds of non-standard pass boxes can be customized according to customer requirements.

Explanation:

- 1. The entrance and exit doors adopt electronic interlocking
- 2. Install lighting fixtures
- 3. The corners of the work area adopt a 20mm diameter circular arc transition for easy cleaning
- 4. The door is made of double-layer tempered glass
- 5. Integrated foaming molding adhesive strip on the door
- 6. Both the interior and top panels are repairable







Dynamic Pass Box



Outside Dimension (W×D×H) (mm)	Inside Dimension (W×D×H) (mm)
600×460×900	400×400×400
700×560×1000	500×500×500
800×660×1100	600×600×600
All binds of non-standard ness house on he sustantiald	

All kinds of non-standard pass boxes can be customized according to customer requirements.

Explanation:

- 1. The entrance and exit doors adopt electronic interlocking
- 2. Install lighting fixtures
- 3. The corners of the work area adopt a 20mm diameter circular arc transition for easy cleaning
- 4. The door is made of double-layer tempered glass
- 5. PAO dust generation and sampling ports are installed on one side of the low cleanliness area
- 6. The self-cleaning time is adjustable, and the usage time of the ultraviolet sterilization lamp can be accumulated or reset to zero
- 7. Integrated foaming molding adhesive strip on the door
- 8. Both the interior and top panels are repairable









Contact us now!



Mobile, Wechat & WhatsApp: +86 13921198925



Email:

katherine.wang@kwangpurification.net kwangpurification@163.com



www.kwangpurification.com www.kwangcleanroom.com www.kwangairshower.com





